

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets											
			Assembled						Un-assembled					
Drager														
Drager Air Boss Evolution Plus PSS 100	30 Min 2216 PSI Carbon	6-9/16"D X 23-5/8"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS						KD-UN or UH or FH-6-SFPHS					
Drager Air Boss Evolution Plus PSS 100	30 Min 2216 PSI Alum - Flat Bottom	6-13/16"D X 24" L (incl valve) Luxfer												
Drager Air Boss Evolution Plus PSS 100	30 Min 4500 PSI Carbon	5-5/16"D X 23"L (incl valve) Carleton	UN or UH-5-30-2-SFPHS						KD-UN or UH or FH-5-SFPHS					
Drager Air Boss Evolution Plus PSS 100	45 Min 4500 PSI Carbon	6.5" D X 22"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS						KD-UN or UH or FH-6-SFPHS					
Drager Air Boss Evolution Plus PSS 100	60 Min 4500 PSI Carbon	6.8" D X 25"L (incl valve) Carleton	UN or UH-7-60-2-SFPHS						KD-UN or UH or FH-7-SFPHS					
Drager Air Boss Evolution	30 Min 2216 PSI Carbon	6-9/16" X 23-5/8"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS						KD-UN or UH or FH-6-SFPHS					
Drager Air Boss Evolution	30 Min 2216 PSI Alum - Flat Bottom	6-13/16"D X 24" L (incl valve) Luxfer												
Drager Air Boss Evolution	30 Min 4500 PSI Carbon	5-5/16"D X 23"L (incl valve) Carleton	UN or UH-5-30-2-SFPHS						KD-UN or UH or FH-5-SFPHS					
Drager Air Boss Evolution	45 Min 4500 PSI Carbon	6.5" D X 22"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS						KD-UN or UH or FH-6-SFPHS					
Drager Air Boss Evolution	60 Min 4500 PSI Carbon	6.8" D X 25"L (incl valve) Carleton	UN or UH-7-60-2-SFPHS						KD-UN or UH or FH-7-SFPHS					
Drager PSS 7000	30 Min 2216 PSI Carbon	6-9/16" X 23-5/8"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS						KD-UN or UH or FH-6-SFPHS					
Drager PSS 7000	30 Min 2216 PSI Alum - Flat Bottom	6-13/16"D X 24" L (incl valve) Luxfer												

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

Drager PSS 7000	30 Min 4500 PSI Carbon	5-5/16"D X 23"L (incl valve) Carleton	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
Drager PSS 7000	45 Min 4500 PSI Carbon	6.5" D X 22"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
Drager PSS 7000	60 Min 4500 PSI Carbon	6.8" D X 25"L (incl valve) Carleton	UN or UH-7-60-2-SFPHS	KD-UN or UH or FH-7-SFPHS
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
GLOBAL				
Global Safety Pioneer	30 Min 4500 PSI Carbon	5.3" D X 23"L (incl valve) Carleton	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
Global Safety Pioneer	45 Min 4500 PSI Carbon	6.5" D X 21"L (incl valve) Carleton	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
Global Safety Pioneer	60 Min 4500 PSI Carbon	6.9" D X 24-3/4"L (incl valve) Carleton	UN or UH-7-30-2-SFPHS	KD-UN or UH or FH-7-SFPHS
INTERSPIRO				
Interspiro Spiromatic S4	30 Min 4500 PSI Carbon	5.4" D X 22"L (incl valve) SCI	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
Interspiro Spiromatic S4	45 Min 4500 PSI Carbon	6.3" D X 23"L (incl valve) Carleton	UN or UH-6-30-1-SFPHS	KD-UN or UH or FH-6-SFPHS
Interspiro Spiromatic S4	60Min 4500 PSI Carbon	6.9" D X 24-1/2"L (incl valve) Carleton	UN or UH-7-60-2-NEFPHS	KD-UN or UH or FH-7-NEFPHS
ISI (Avon-ISI)				
ISI (Avon) Viking DXL	30 Min 4500 PSI Carbon	5.4" D X 23-1/4"L (incl valve) Carleton	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
ISI (Avon) Viking DXL	45 Min 4500 PSI Carbon	6.4" D X 23"L (incl valve) Carleton	UN or UH-6-30-1-SFPHS	KD-UN or UH or FH-6-SFPHS

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

ISI (Avon) Viking DXL	60Min 4500 PSI Carbon	6.-7/8" D X 24-3/4"L (incl valve) Carleton	UN or UH-7-60-2-SFPHS	KD-UN or UH or FH-7-SFPHS
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
ISI (Avon-ISI)				
ISI (Avon) Viking Z-7	30 Min 2216 PSI Carbon	6-9/16"D X 23-1/2"L (incl valve) Carleton		
ISI (Avon) Viking Z-7	30 Min 4500 PSI Carbon	5.3" D X 23-1/4"L (incl valve) Carleton		
ISI (Avon) Viking Z-7	45 Min 4500 PSI Carbon	6.4" D X 23"L (incl valve) Carleton		
ISI (Avon) Viking Z-7	60Min 4500 PSI Carbon	6.-7/8" D X 24-1/2"L (incl valve) Carleton		
MSA				
MSA Firehawk	30Min 2216 PSI Carbon	6.75" D X 22-1/4"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Firehawk	30Min 3000 PSI Carbon	6.75" D X 23-1/2"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Firehawk	30Min 4500 PSI Carbon	5.4" D X 21-1/2"L (incl valve) Luxfer	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
MSA Firehawk	45 Min 4500 PSI Low Profile Carbon	6.3" D X 23-1/4"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Firehawk	45 Min 4500 PSI Stubby Carbon	6.8" D X 21-1/4"L (incl valve) Luxfer	UN or UH-6-30-3-SFPHS	KD-UN or UH or FH-6-SFPHS

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
MSA (Con't)				
MSA Firehawk	60Min 4500 PSI Carbon	7.1" D X 24"L (incl valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-UN _{or} UH _{or} FH-7-SFPHS
MSA Firehawk M-7	30Min 2216 PSI Carbon	6.75" D X 22-1/4"L (incl valve) Luxfer	UN _{or} UH-6-30-2-SFPHS	KD-UN _{or} UH _{or} FH-6-SFPHS
MSA Firehawk M-7	30Min 3000 PSI Carbon	6.75" D X 23-1/2"L (incl valve) Luxfer	UN _{or} UH-6-30-2-SFPHS	KD-UN _{or} UH _{or} FH-6-SFPHS
MSA Firehawk M-7	30Min 4500 PSI Carbon	5.4" D X 21-1/2"L (incl valve) Luxfer	UN _{or} UH-5-30-2-SFPHS	KD-UN _{or} UH _{or} FH-5-SFPHS
MSA Firehawk M-7	45 Min 4500 PSI Low Profile Carbon	6.3" D X 23-1/4"L (incl valve) Luxfer	UN _{or} UH-6-30-2-SFPHS	KD-UN _{or} UH _{or} FH-6-SFPHS
MSA Firehawk M-7	45 Min 4500 PSI Stubby Carbon	6.8" D X 21-1/4"L (incl valve) Luxfer	UN _{or} UH-6-30-3-SF	KD-UN _{or} UH _{or} FH-6-SF
MSA Firehawk M-7	60Min 4500 PSI Carbon	7.1" D X 24"L (incl valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-UN _{or} UH _{or} FH-7-SFPHS

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
MSA (Con't)				
MSA Stealth	30Min 2216 PSI Carbon	6.75" D X 22-1/4"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Stealth	30Min 3000 PSI Carbon	6.75" D X 23-1/2"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Stealth	30Min 4500 PSI Carbon	5.4" D X 21-1/2"L (incl valve) Luxfer	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS
MSA Stealth	45 Min 4500 PSI LowProfile Carbon	6.3" D X 23-1/4"L (incl valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Stealth	45 Min 4500 PSI Stubby Carbon	6.8" D X 21-1/4"L (incl valve) Luxfer	UN or UH-6-30-3-SFPHS	KD-UN or UH or FH-6-SFPHS
MSA Stealth	60Min 4500 PSI Carbon	7.1" D X 24"L (incl valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-UN or UH or FH-7-SFPHS
Scott				
Scott AP-50	30Min 2216 PSI Carbon	6-9/16" D X 23-1/2"L (incl valve) Luxfer	UN or UH-6-30-1-SFPHS	KD-UN or UH or FH-6-SFPHS
Scott AP-50	30Min 4500 PSI Carbon	5.4" D X 21-1/2"L (incl valve) Luxfer	UN or UH-5-30-2-SFPHS ** SC-50-H-5-SFPHS **Best bracket for this application	KD-UN or UH or FH-5-SFPHS ** KD-LP-5-SFPHS **Best bracket for this application
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Scott (Con't)				

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

Scott AP-50	45Min 4500 PSI Low Profile Carbon	6.2" D X 23-1/4"L (incl valve) SCI	UN or UH-6-30-1-SFPHS ** SC-50-H-6-SFPHS **Best bracket for this application	KD-UN or UH or FH-6-SFPHS ** KD-LP-6-SFPHS **Best bracket for this application
Scott AP-50	45Min 4500 PSI Stubby Carbon	6.8" D X 21-1/4"L (incl valve) Luxfer	SC-50-H-6-SFPHS	
Scott AP-50	60Min 4500 PSI Carbon	6-7/8" D X 24-3/4"L (incl valve) Luxfer	SC-50-H-7-SFPHS	KD-UN or UH or FH-7-SFPHS
Scott AP-75	30Min 2216 PSI Carbon	6-9/16"D X 23-1/2"L (incl valve) Luxfer	UN or UH-6-30-1-SFPHS	KD-UN or UH or FH-6-SFPHS
Scott AP-75	30Min 5500PSI Carbon	6-15/16"D X 22"L (incl valve) Luxfer	SC-50-FH-5-SFPHS	KD-FHLP-5-SFPHS
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Scott (Con't)				
Scott AP-75	45Min 4500 PSI Low Profile Carbon	6.2" D X 23-1/2"L (inc valve) SCI	SC-50-H-6-SFPHS	

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

Scott AP-75	45Min 4500 PSI Stubby Carbon	6.8"D X 21-1/4"L (Inc Valve) Luxfer	SC-50-H-6-SFPHS	
Scott AP-75	60Min 4500 PSI Carbon	6-7/8"D X 24-3/4"L (Inc Valve) Luxfer	UN or UH-7-60-3-SFPHS **SC-50-H-7-SFPHS **Best bracket for this application	KD-UN or UH or FH-7-SFPHS
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Scott (Con't)				
Scott NXG2	30Min 2216 PSI Carbon	6-9/16"D X 23-1/2"L (Inc valve) Luxfer	SC-50-LP-6-SFPHS	KD-LP-6-SFPHS
Scott NXG2	30Min 4500 PSI Carbon	5.4" D X 21-1/2" (Inc Valve) Luxfer	SC-50-LP-5-SF (recommend adding -PHS Option)	KD-LP-5-SF (recommend adding -PHS Option)

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

Scott NXG2	45Min 4500 PSI LowProfile Carbon	6.2" D X 23-1/2"L (Inc valve) SCI	SC-50-LP-6-SFPHS	KD-LP-6-SFPHS
Scott NXG2	45Min 4500 PSI Stubby Carbon	6.8"D X 21-1/4"L (Inc Valve) Luxfer	SC-50-LP-6-SFPHS	
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Scott (Con't)				
Scott NXG2	60Min 4500 PSI Carbon	6-7/8"D X 24-3/4"L (Inc Valve) Luxfer	SC-50-LP-6-SFPHS	KD-LP-6-SFPHS
Scott NXG7	30Min 2216 PSI Carbon	6-9/16"D X 23-1/2"L (Inc Valve) Luxfer	SC-50-LP-6-SFPHS	KD-LP-6-SFPHS
Scott NXG7	30Min 4500 PSI Carbon	5.4" D X 21-1/2"L (Inc Valve) Luxfer	SC-50-H-5-SFPHS	KD-LP-5-SFPHS

Recommended Walkaway Brackets (by SCBA) for Wall Mounting and Apparatus Side Compartments

Scott NXG7	45Min 4500 PSI LowProfile Carbon	6.2" D X 23-1/2"L (Inc valve) SCI	SC-50-LP-6-SFPHS	KD-LP-6-SFPHS
Scott NXG7	45Min 4500 PSI Stubby Carbon	6.8"D X 21-1/4"L (Inc Valve) Luxfer	SC-50-H-6-SFPHS	
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Survivair/Sperian				
Sperian (Survivair) Panther	30Min 2216 PSI Carbon	6.56" D X 23"L (Inc Valve) Luxfer	UN or UH-6-30-2-SFPHS	KD-UN or UH or FH-6-SFPHS KD-LP-6-SFPHS
Sperian (Survivair) Panther	30Min 4500 PSI Carbon	5.4" D X 21-3/4"L (Inc Valve) Luxfer	UN or UH-5-30-2-SFPHS	KD-UN or UH or FH-5-SFPHS **KD-LP-5-SFPHS **Best bracket for this application
Sperian (Survivair) Panther	45Min 4500 PSI Carbon	6.25" D X 23"L (Inc Valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-UN or UH or FH-6-SFPHS **KD-LP-6-SFPHS **Best bracket for this application
Sperian (Survivair) Panther	45Min 4500 PSI Carbon	6.75" D X 20-3/4"L (Inc Valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-LP-6-SFPHS
Sperian (Survivair) Panther	60Min 4500 PSI Carbon	6.85" D X 24-1/2"L (Inc Valve) Luxfer	Assembled bracket not available for this SCBA / Air Cylinder combination	KD-UN or UH or FH-6-SFPHS **KD-LP-6-SFPHS **Best bracket for this application
SCBA Type	AirCyl Type	AirCyl Dim / Manuf	Recommended Brackets	
			Assembled	Un-assembled
Survivair/Sperian (Con't)				

